

|                |             |                     |
|----------------|-------------|---------------------|
| LOC/DME I-AAAY | APP CRS     | Rwy Ldg             |
| <b>110.3</b>   | <b>227°</b> | <b>8273</b>         |
| Chan <b>40</b> |             | TDZE <b>262</b>     |
|                |             | Apt Elev <b>266</b> |

ILS or LOC RWY 22R


BILL AND HILLARY CLINTON NTL/ADAMS FLD (LIT)

Simultaneous approach authorized. For inop ALS, increase S-LOC 22R Cat C/D visibility to 1½ SM; increase GOHKO Fix Minimums (DME required) S-LOC 22R Cat C/D visibility to RVR 6000.

ALSF-2

MISSED APPROACH: Climb to 1000 then climbing right turn to 3000 on LIT VORTAC R-247 to BEGAN INT/LIT 28.7 DME and hold.

|               |                     |                    |                    |
|---------------|---------------------|--------------------|--------------------|
| D-ATIS        | LITTLE ROCK APP CON | ADAMS TOWER        | GND CON            |
| <b>125.65</b> | <b>135.4 353.6</b>  | <b>118.7 257.8</b> | <b>121.9 339.8</b> |



ELEV 266

D

TDZE 262

1000

3000

BEGAN

SHERR INT  
I-AAAY 7.4  
LIT 1.1

Remain within 10 NM

047°

227°

2200

GS 3.00°  
TCH 59

Use I-AAAY DME when on the localizer course.

IM

GOHKO  
I-AAAY 2.8

740

I-AAAY 1.5

81

6224 X 150

227°

36

40

8231 X 150

TWR

MIRL Rwy 18-36

HIRL Rwys 4R-22L and 4L-22R

TDZL/RCLS Rwy 22R

FAF to MAP 5.9 NM

|         |      |      |      |      |      |
|---------|------|------|------|------|------|
| Knots   | 60   | 90   | 120  | 150  | 180  |
| Min:Sec | 5:54 | 3:56 | 2:57 | 2:22 | 1:58 |

|                                   |                      |                       |                          |                        |
|-----------------------------------|----------------------|-----------------------|--------------------------|------------------------|
| CATEGORY                          | A                    | B                     | C                        | D                      |
| S-ILS 22R                         | 462/18 200 (200-½)   |                       |                          |                        |
| S-LOC 22R                         | 740/24               | 478 (500-½)           | 740/50                   | 478 (500-1)            |
| CIRCLING                          | 820-1<br>554 (600-1) | 1000-1<br>734 (800-1) | 1180-2¾<br>914 (1000-2¾) | 1180-3<br>914 (1000-3) |
| GOHKO FIX MINIMUMS (DME REQUIRED) |                      |                       |                          |                        |
| S-LOC 22R                         | 680/24               | 418 (500-½)           | 680/40                   | 418 (500-¾)            |
| CIRCLING                          | 820-1<br>554 (600-1) | 1000-1<br>734 (800-1) | 1180-2¾<br>914 (1000-2¾) | 1180-3<br>914 (1000-3) |